



Washer extractor W4850H, W41100H

Features and benefits

- Clarus Control® programmable microprocessor with 9 fixed and up to 192 programs to allow free programming
- · High extraction for efficient dewatering
- · Frequency-controlled motor for optimal washing
- · Supplied with 8 + 5 signals for liquid detergents
- · Eight connections for liquid detergents
- · Large door opening for easy loading and unloading
- All critical parts made from stainless steel to provide a high level of corrosion resistance
- · Powder painted galvanised steel side panels
- Bearing seals lubricated with oil to ensure a long service life.
 Empty container alarm
- Direct steam heating.
- · Low noise level for pleasant working environment
- · Designed for easy servicing and maintenance

Main options

- Forward or forward/backward tilting with full reversing function
- · Noise/heat insulation
- · Test tap with level tube
- Two drain valves for recovering water/wash solution
- Five-compartment injector for powder detergent (located at the front or on the right hand side of the machine)
- · Third water valve
- Large water valves
- · IS Integrated Saving
- Connection for intelligent detergent system (DMIS)
- · Connection to CMIS



Images shown are a representation of the product only and variations may occur.

Main specifications			W4850H	W41100H
Max. capacity		kg/lb	90/200	120/250
Drum, volume		litre	850	1100
diamete	er	ø mm	1220	1220
Extraction		rpm	720	663
G-factor			350	300
Heating alternatives	steam		X	×
	non-heated		X	×
	electricity	kW	-	_
Consumption data "No	ormal 60°C"			
Total time (cold+hot/cold)		min	45/50	45/50
Water consumption (cold/hot)		litre	713/125	850/153
Energy consumption (motor/heating)		kWh	2.3/-	2.4/-
Steam consumption (cold/hot)		kg	10	12
Steam consumption (cold)		kg	19	23
Water temperature 15°C cold water and 65°C hot water.				



Electrical connections			W4850H	W41100H
Steam or non-heated	200V 3AC 60 Hz 230V 3AC 50 Hz 230V 3AC 60 Hz 400-415V 3N AC 50 Hz	kW(A) kW(A) kW(A)	6.7 (35) 6.7 (25) 6.7 (20) 6.7 (16)	5.3 (35) 5.3 (25) 5.3 (20) 5.3 (16)
Water, steam and air connections		- (· -)	()	
Water valves Rec. Water pressure Function limits for water valve Capacity at 300 kPa Drain valve		DN kPa kPa l/min ø mm l/min DN kPa L/h DN	32 200-600 50-1000 150 110 400 32 300-600 50-800 6 500-700 20	32 200-600 50-1000 150 110 400 32 300-600 50-800 6 500-700 20
Floor requirements				
Frequency of the dynamic force Floor load at max extraction		Hz kN	12.0 25.9 ± 1.5	11.1 27.9 <u>±</u> 2.0
Sound levels	S			
Sound level Sound level, with insulation		dB(A) dB(A)	73 < 70	73 < 70
Heat emission				
% of installed power, max 90°		6.7	6.8	
Shipping data				
Shipping volu	ume	net, kg m³	2200 7.6	2300 8.4

Other voltages available, see installation manual.








Unit 3 / 41 Biscayne Way, Jandakot, WA 6164 Ph: (08) 9414 9474 Fax: (08) 6210 5961 Service: 0411 883 346 / 0400 246 352 Sales: 0406 659 429/ sales@comls.com.au


Web site : www.comls.com.au





Dimensions in mm	W4850H	W41100H
A Width	1640	1640
B Depth	1635	1850
C Height std/tilt+IWS	2190/2230	2190/2230
D std/tilt+IWS	955/995	955/995
Ea	300	300
Eb	380	380
F std/tilt+IWS	2095/2135	2095/2135
G	1070	1070
H	830	830
1	635	635
K	445	445
L	1140	1140
M std/tilt+IWS	1620/1660	1660/1660
N std/tilt+IWS	395/435	395/435
0	820	820
P	2410	2400
R	1175	1160
S	2480	2480
T	960	955
U	285	240
V	400	335

- 1 Control panel
- 2 Door opening ø 700 mm
- **3a**Five-compartment detergent injector for powder detergent, front (optional)
- **3b**Five-compartment detergent injector for powder detergent, right hand side (optional)
- 4 Cold water connection
- 5 Hot water connection
- 6 Third water connection (optional)
- **7** Steam connection
- 8 Drain
- 9 Electrical connection
- 10 Compressed air connection
- 11 External liquid detergent injector, 6 pcs ø 10, 1 pc ø 16 and 1 pc ø 20
- 12 Water connection, detergent injector (optional)











Options

- Forward or forward/backward tilting with drum reversal makes unloading into a trolley easy.
- · Noise/heat insulation reduces airborne noise to less than 70 dB(A).
- · Test tap with level tube allows you to take samples from the wash solution.
- Water/wash solution recovery system two drain valves allow you to recover rinse water and re-use it in the
 wash
- Five-compartment injector for powder detergent
 Option 1, (5x1 litre), located on front of the machine.
 Option 2, (5x2 litres), located on right hand side of the machine.
- · Water inlet via pump additional water inlet for water via pump from recovery system.
- Third water valve electrically-controlled water valve for hard water.
- Steam connection components.
- Connection components for 2 water connections.
- · Connection components for 3 water connections.
- · Pump inlet connection components. Recovery
- IS Integrated Saving
- · Connection for intelligent detergent system (DMIS).
- · Large water valves (DN 50 / 2" BSP) (DN 40 / 1 1/2" BSP).
- · May be included in a hands-off system.
- · Kit for connection to CMIS (Certus Management Information Systems) network.

Accessory

 WPM PC program. Allows the creation of wash programs on a PC and their transference to the machine via a memory card.



CMIS can be fitted to washer extractors with Clarus Control, tumble dryers with Selecta Control and ironers with electronic control system. All you need to access and view the statistical feedback is a normal PC.

Art No. 438901961/2015.01.14

We reserve the right to alter specifications without notice.





Unit 3 / 41 Biscayne Way, Jandakot, WA 6164 Ph: (08) 9414 9474 Fax: (08) 6210 5961 Service: 0411 883 346 / 0400 246 352

Sales : 0406 659 429/ <u>sales@comls.com.au</u>

Web site: www.comls.com.au